



### Medium handle brush - White - Soft bristle

Brush with shaped handgrip for cleaning equipment with regular work surfaces.



| Code          | Colour | Size (mm)     | Material | Bristle (mm) | Bristle height (mm) | Net weight (kg) |
|---------------|--------|---------------|----------|--------------|---------------------|-----------------|
| <b>1005WS</b> | White  | 390 x 55 x 70 | PP - PBT | Soft - Ø 0,3 | 55                  | 0,22            |

### Usage information

|                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Minimum and maximum temperature | min -20 / max 80 C°                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Washing (dishwasher)            | 80° C for 8 min (recommended)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Autoclave                       | 121° C for 20 min                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| User and maintenance manual     | <ul style="list-style-type: none"> <li>- Remove packaging and any label from tools and disinfect them.</li> <li>- Both manual and autoclave disinfection is possible.</li> <li>- Sanitize tools using appropriate chemical decontamination products, in the concentrations, times and temperatures provided.</li> <li>- Make sure tools completely dry up before next use.</li> <li>- Hang tools while drying up to avoid any contamination, breakage or bristles distortion.</li> <li>- The storing area must be clean and far away from sources of intense light or heat.</li> <li>- Do not use damaged tools, both supports and bristles must be in a good state.</li> </ul> |

### Compliance

- REACH
- FDA
- EU 1935/2004 and updates
- EU 2023/2006 and updates
- EU 10/2011 and updates

### Logistical information

|                         |                 |                        |                |
|-------------------------|-----------------|------------------------|----------------|
| Internal packaging type | Poly bag        | Product barcode        | 8008805105410  |
| External packaging type | Carton          | Box barcode            | 08008805105410 |
| Quantity per pack (pcs) | 12              | Customs tariff         | 96039091       |
| Box gross weight (kg)   | 2,94            | Country of origin      | Italy          |
| Box dimensions (mm)     | 400 x 210 x 165 | Palletising (pcs)      | 1008           |
| Box volume (m³)         | 0,01386         | Pallet dimensions (cm) | 125 x 82 x 130 |

### Available versions

|        |                                                             |              |                               |
|--------|-------------------------------------------------------------|--------------|-------------------------------|
| Size   |                                                             | Bristle type | Tough - Ø 0,75   Medium Ø 0,5 |
| Colour | <span>B</span> <span>R</span> <span>Y</span> <span>G</span> | Material     | Detectable                    |