



### Long handle brush - Green - Medium bristle

Ideal brush to get into the furthest places and deepest containers.



| Code          | Colour | Size (mm)     | Material | Bristle (mm)   | Bristle height (mm) | Net weight (kg) |
|---------------|--------|---------------|----------|----------------|---------------------|-----------------|
| <b>1006GM</b> | Green  | 450 x 60 x 85 | PP - PBT | Medium - Ø 0,5 | 45                  | 0,25            |

### Usage information

|                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Minimum and maximum temperature | min -20 / max 80 C°                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Washing (dishwasher)            | 80° C for 8 min (recommended)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Autoclave                       | 121° C for 20 min                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| User and maintenance manual     | <ul style="list-style-type: none"> <li>- Remove packaging and any label from tools and disinfect them.</li> <li>- Both manual and autoclave disinfection is possible.</li> <li>- Sanitize tools using appropriate chemical decontamination products, in the concentrations, times and temperatures provided.</li> <li>- Make sure tools completely dry up before next use.</li> <li>- Hang tools while drying up to avoid any contamination, breakage or bristles distortion.</li> <li>- The storing area must be clean and far away from sources of intense light or heat.</li> <li>- Do not use damaged tools, both supports and bristles must be in a good state.</li> </ul> |

### Compliance

- REACH
- FDA
- EU 1935/2004 and updates
- EU 2023/2006 and updates
- EU 10/2011 and updates

### Logistical information

|                         |                 |                        |                  |
|-------------------------|-----------------|------------------------|------------------|
| Internal packaging type | Poly bag        | Product barcode        | 8008805106226    |
| External packaging type | Carton          | Box barcode            | 08008805106226   |
| Quantity per pack (pcs) | 12              | Customs tariff         | 96039091         |
| Box gross weight (kg)   | 3,36            | Country of origin      | Italy            |
| Box dimensions (mm)     | 505 x 210 x 170 | Palletising (pcs)      | 756              |
| Box volume (m³)         | 0,0180285       | Pallet dimensions (cm) | 120 x 80 x 133,5 |

### Available versions

|        |                                                                                                                                                                                                                                                                                                                                                                                                                         |              |                |
|--------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|----------------|
| Size   |                                                                                                                                                                                                                                                                                                                                                                                                                         | Bristle type | Tough - Ø 0,75 |
| Colour | <span style="background-color: #00AEEF; color: white; border-radius: 50%; padding: 2px 5px;">B</span> <span style="background-color: #D62728; color: white; border-radius: 50%; padding: 2px 5px;">R</span> <span style="background-color: #FFD700; color: black; border-radius: 50%; padding: 2px 5px;">Y</span> <span style="background-color: #A9A9A9; color: black; border-radius: 50%; padding: 2px 5px;">W</span> | Material     | Detectable     |